

Обычные рефрактометры

Технические характеристики

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: hyp@nt-rt.ru || сайт: <https://huixiasupply.nt-rt.ru/>

Common hand held refractometer



Item	Common hand held refractometer
Brand Name	HUIXIA
Model Number	See below table
Waterproof	No
Place of Origin	Fuzhou, China
Supply Ability	5000pcs per month
Package	plastic box/leather box/cloth box
Shipping method	DHL/UPS/FEDEX/TNT/by air/by sea
Port	Fuzhou, China
Trade terms	FOB/CIF/CNF
Payment method	paypal/bank transfer/west union

Tags: refraktometer,refractometer,hand held meter,autorefractor,refractometer brix,refractometre abbe,abbe

Features:

Determines the concentration of test liquid sample
 Approved by strict quality and safety standards
 Durable and built to last a long time
 Heavy and lightweight with aluminum construction
 Easy to focus and calibrate
 Accurate testing results are guaranteed
 Made with the highest and most accurate quality of aluminum & rubber, making it easy
 Soft with soft and comfortable non-slip rubber
 Extremely easy to use and calibrate

Specification:

Series	Model	Range	Accuracy
Brix/ATC	SBR0005	0~5%	0.10%
	SBR0010	0-10%	0.10%
	SBR0020	0~20%	0.10%
	SBR0032	0~32%	0.20%
	SBR2862	28~62%	0.20%
	SBR4582	45~82%	0.50%
	SBR5892	58~92%	0.50%
	SBR0050	0~50%	0.50%
	SBR0080	0~80%	0.50%
	SBR0090	0-90%	0.50%
Honey/ATC	SHN1325	13~25% Honey Moisture	0.10%
	SBR5890	58~90% brix 12~27% water 38~43 Be'	0.50% 1% 0.005
Salinity /ATC	SSA0010	Salinity:0~100‰	Salinity:1‰

		1.000~1.070sg	0.001sg
	SSA2832	Salinity0~28%, Brix 0-32%	0.20%
	SSA0028	Salinity0~28%	0.20%
Clinical Protein/ATC	SUR-1	SP: 0~12g/100ML U.G: 1.000~1.040 nD: 1.3330~1.3600	0.2g/100mL 0.002sg 0.0002
	SUR-2	SP: 0~12g/dl U.G: 1.000~1.050	0.2g/dl 0.0005ND
	SUR-3	SP: 0~12g/100ML U.G: 1.000~1.050 nD: 1.3330~1.3600	0.2g/100mL 0.002sg 0.0002
Battery /Antifreeze /Cleaning Fluid /AdBlue /ATC	SBC-1	B: 1.100-1.400sg E: -50°C-0°C P: -50°C-0°C C: -40°C-0°C	0.01sg 1°C 1°C 5°C
	SBC-2	D: 0~100% E: -60°C-0°C B: 1.100-1.400sg	5% 5°C 0.01sg
	SBC-5	Adblue:30-35% B: 1.100-1.400sg E: -50°C-0°C P: -50°C-0°C C: -40°C-0°C	5% 0.01sg 5°C 5°C 5°C
	SBC-6	EG:-60°C-0°C PG:-50°C-0°C BA: 1.100-1.400sg	EG:5°C PG:5°C BA: 0.01sg
	SBC-7	EG:-60°F-32°F PG:-50°F-32°F BA: 1.15-1.30sg	EG:10°F PG:10°F BA: 0.01sg
	SBC-8	EG:-84°F-32°F PG:-60°F-32°F BA: 1.100-1.400sg	EG:5°F PG:5°F BA: 0.01sg
	SBC-9	Adblue:0-40%	0.10%
	SBC-10	Adblue:30-35% B: 1.100-1.300sg E: -50°C-0°C P: -50°C-0°C C: -40°C-10°C	0.5% 0.01sg 1°C 1°C 1°C
Alcohol /ATC	SAL0080	0~60%, 60~80% V/V	1%, 2%
	SAL2025	0-20 Baume, 0-25%vol	0.2 Baume, 0.2% Vol
	SAL2040	0-20 Baume, Brix 0-40%	0.2 Baume, 0.2% Brix
	SAL2540	0~25%Vol, 0-40%Brix	0.2% Vol/Brix
	SAL0025	0~25%Vol	0.20%
	SAL2540-Be	0-20 Baume, 0-25%vol,0-40%Brix	0.2 Baume, 0.2% Vol/Brix
Milk/ATC	SMK-1	0~20%	0.002
Beer/ ATC	SBR0032SG	Brix: 0-32% WortSG:1.000-1.120	Brix: 0.20% WortSG:±0.003

OE/ATC	SBR-32S	0~140 Oe	1 Oe
		0~25KMW(Babo)	0.2KMW(Babo)
	SBR-44S	0~32%Mas Sacch	0.2%Mas Sacch
		0-44%Brix	0.5%Brix
		0-190 °Oe	2.0 °Oe
		0-38° KMW Babo	0.5°KMW Babo

Packing list:

- 1 * Refractometer
- 1 * Operation Manual
- 1 * Mini screwdriver
- 1 * Pipettes
- 1* Clean cloth

Application:

HUIXIA common hand held refractometer can be used in Aquarium industry, beer/wine brew industry, medical industry, food industry, farm, honey industry, auto parts industry, water analysis industry, liquid analysis industry, pet industry and so on.

По вопросам продаж и поддержки обращайтесь:

Алматы (727)345-47-04
Ангарск (3955)60-70-56
Архангельск (8182)63-90-72
Астрахань (8512)99-46-04
Барнаул (3852)73-04-60
Белгород (4722)40-23-64
Благовещенск (4162)22-76-07
Брянск (4832)59-03-52
Владивосток (423)249-28-31
Владикавказ (8672)28-90-48
Владимир (4922)49-43-18
Волгоград (844)278-03-48
Вологда (8172)26-41-59
Воронеж (473)204-51-73
Екатеринбург (343)384-55-89

Иваново (4932)77-34-06
Ижевск (3412)26-03-58
Иркутск (395)279-98-46
Казань (843)206-01-48
Калининград (4012)72-03-81
Калуга (4842)92-23-67
Кемерово (3842)65-04-62
Киров (8332)68-02-04
Коломна (4966)23-41-49
Кострома (4942)77-07-48
Краснодар (861)203-40-90
Красноярск (391)204-63-61
Курск (4712)77-13-04
Курган (3522)50-90-47
Липецк (4742)52-20-81

Магнитогорск (3519)55-03-13
Москва (495)268-04-70
Мурманск (8152)59-64-93
Набережные Челны (8552)20-53-41
Нижний Новгород (831)429-08-12
Новокузнецк (3843)20-46-81
Ноябрьск (3496)41-32-12
Новосибирск (383)227-86-73
Омск (3812)21-46-40
Орел (4862)44-53-42
Оренбург (3532)37-68-04
Пенза (8412)22-31-16
Петрозаводск (8142)55-98-37
Псков (8112)59-10-37
Пермь (342)205-81-47

Ростов-на-Дону (863)308-18-15
Рязань (4912)46-61-64
Самара (846)206-03-16
Санкт-Петербург (812)309-46-40
Саратов (845)249-38-78
Севастополь (8692)22-31-93
Саранск (8342)22-96-24
Симферополь (3652)67-13-56
Смоленск (4812)29-41-54
Сочи (862)225-72-31
Ставрополь (8652)20-65-13
Сургут (3462)77-98-35
Сыктывкар (8212)25-95-17
Тамбов (4752)50-40-97
Тверь (4822)63-31-35

Тольятти (8482)63-91-07
Томск (3822)98-41-53
Тула (4872)33-79-87
Тюмень (3452)66-21-18
Ульяновск (8422)24-23-59
Улан-Удэ (3012)59-97-51
Уфа (347)229-48-12
Хабаровск (4212)92-98-04
Чебоксары (8352)28-53-07
Челябинск (351)202-03-61
Череповец (8202)49-02-64
Чита (3022)38-34-83
Якутск (4112)23-90-97
Ярославль (4852)69-52-93

Россия +7(495)268-04-70

Казахстан +(727)345-47-04

Беларусь +(375)257-127-884

Узбекистан +998(71)205-18-59

Киргизия +996(312)96-26-47

эл.почта: hyp@nt-rt.ru || сайт: <https://huixiasupply.nt-rt.ru/>